


Technical data sheet

Series terminals 16 mm², polypropylene

Item number: 2056724



Tested according to EN 60998. Steel terminals, steel screws, electrogalvanised, 12-pin, individual terminals detachable from strips using "twist'n'pull". Captive upwards screw. Max. approved ambient temperature to EN 60998: -5 to +80 °C. Nominal cross-section 16 ÷ mm² Nominal voltage 450 V Nominal current 76 A Max. connections per side: 16 mm² rigid or 10 mm² flexible or 6 mm² flexible.



PP Polypropylene

Master data

Item number	2056724
Type	78 CE WS/ORLK 16
Description 1	Terminal strip
Available from	01.12.2025
Manufacturer	OBO
Dimension	16mm ²
Colour	White
Material	Polypropylene
Smallest sales unit	10
Unit of quantity	Piece
Weight	6.64 kg
Weight unit	kg/100 pc.

Technical data sheet

Series terminals 16 mm², polypropylene

Item number: 2056724



Dimensions



Length	175 mm
Width	25 mm
Height	20.7 mm

Technical data

Closing plate required	no
Connectable conductor cross-section, fine-wire with wire-end ferrule, max.	16 mm ²
Connectable conductor cross-section, fine-wire with wire-end ferrule, min.	4 mm ²
Connectable conductor cross-section, fine-wire without wire-end ferrule, max.	6 mm ²
Connectable conductor cross-section, fine-wire without wire-end ferrule, min.	4 mm ²
Connectable conductor cross-section, multi-wire, max.	10 mm ²
Connectable conductor cross-section, multi-wire, min.	4 mm ²
Connection position	Side
No. of terminals	12
Number of screwless terminals per pole	2
Version of electrical connection 1	Screw connection
Version of electrical connection 2	Screw connection
Drill hole spacing, centre	15 mm
Explosion-tested version	no
Suitable for flexible conductors	yes
Suitable for solid conductors	yes
Suitable for multi-wire conductors	yes
Mounting type	Direct mounting
Nominal cross-section, min.	16 mm ²
Nominal voltage	450 V
Nominal current	76 A
Pole number	12
Cross-section	Max. connections per side: 16 mm ² rigid or 10 mm ² flexible or 6 mm ² flexible mm ²
ROHS-conformant	yes
Screw tightening torque	1.2 Nm

Technical data sheet

Series terminals 16 mm², polypropylene

Item number: 2056724



Technical data

Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-5 °C
Transparent	no
Ambient temperature	80 °C