

Technical data sheet

A 11 junction box, OBO EcoLine

Item number: 2000344



Protection class IP55, nominal voltage 690 V, nominal cross-section 2.5 mm², 12 entries for cable diameter 5–14 mm.
Clamshell.
Dimensions: 85 x 85 x 40 mm.
Internal clearance: 75 x 75 x 35 mm
For every 10 sockets 1 cutting tool



Master data

Item number	2000344
Type	A 11 ECO
Description 1	Junction box
Available from	06.03.2026
Manufacturer	OBO
Dimension	85x85x40
Colour	Light grey; RAL 7035
Material	Polyethylene Eco
Smallest sales unit	10
Unit of quantity	Piece
Weight	4.446 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,0592 kg CO2e / 1 Piece



Technical data sheet

A 11 junction box, OBO EcoLine

Item number: 2000344



Dimensions



Length	85 mm
Width	85 mm
Height	40 mm

Technical data

Expandable	yes
No. of entries	12
Type of entry	Cable
Type of entry	Cable
Type of housing penetration	Pre-marking
Measured insulation voltage V_i	690 V
Equipment	Without
Cover	Not transparent
Cover fastening	Locking
Entry from rear	no
Entries	12 entries for cable diameter 5–14 mm
Explosion-tested version	no
Flame-resistant	acc. to VDE 0471/DIN 695 Part 2-1, test temperature 650°C
Shape	Square
Maintain electrical functions	Without
For Ex zone	Without
For Ex zone gas	Without
For Ex zone dust	Without
for pipe diameter	14 mm
Halogen-free	yes
Clear internal dimensions	75x75x35 mm
Max. Conductor cross-section	2.5 mm ²
With screening	no
with lid	yes
Mounting in the earth	no
Mounting underwater	no
Mounting type	Wall/ceiling mounting
Nominal cross-section, min.	2.5 mm ²
Nominal voltage	690 V
Sealable	no
Protection rating	IP55
Permitted temperature range, max.	45 °C
Permitted temperature range, min.	-5 °C
Transparent lid	no

Technical data sheet

A 11 junction box, OBO EcoLine

Item number: 2000344



Technical data

Castable	no
Sealing compound supplied	no
Weatherproof	no