

# Technical data sheet

## Collecting clamp Grip M UNI, metal FS, for direct fastening

Item number: 2207210



Metal collection clamp for laying cables on walls or ceilings. Direct fastening via a plastic adapter or via classic screw mounting through a separate fastening hole  $\varnothing 6 \text{ mm}$ . Universal adapter for single-handed mounting with various firing tools, such as from Hilti, Würth, Spit, Bosch. High mechanical resistance also in the event of fire. Halogen-free, non-combustible. Suitable for safe mounting above fire protection ceilings. Also approved as a cable-specific variant for the maintenance of electrical functionality to DIN 4102 part 12. The lock can be opened without tools. Detailed information on the approved routing variants can be found in the appropriate testing documentation.



|    |                  |
|----|------------------|
| St | Steel            |
| FS | Strip galvanised |

### Master data

|                     |                       |
|---------------------|-----------------------|
| Item number         | 2207210               |
| Type                | 2031 M UNI 10 FS      |
| Description 1       | Grip collecting clamp |
| Description 2       | for direct fastening  |
| Manufacturer        | OBO                   |
| Dimension           | 10x NYM3x1,5          |
| Colour              | zinc                  |
| Material            | Steel                 |
| Surface             | Strip galvanised      |
| Surface standard    | DIN EN 10346          |
| Smallest sales unit | 50                    |
| Unit of quantity    | Piece                 |
| Weight              | 3.58 kg               |
| Weight unit         | kg/100 pc.            |


Technical data sheet

Collecting clamp Grip M UNI, metal FS, for direct fastening

Item number: 2207210



Dimensions



Technical data

|                               |     |
|-------------------------------|-----|
| No. of conductors NYM 3 x 1.5 | 10  |
| Maintain electrical functions | yes |
| Halogen-free                  | yes |
| With anchor                   | no  |