


Technical data sheet

Equipotential busbar, solid version

Item number: 5015057



- Base plate and screw-on cover made of strip-galvanised steel
- Sealable / labellable cover
- Contact strip made of strip-galvanised steel
- Screws and crossbar made of steel, hot-dip galvanised or electrogalvanised

Connection options:

- 6 cables 6-16 mm²
- 1 round conductor Rd 8-10
- 1 flat conductor to FL 40
- 2 cable shoe M8

St	Steel
F	Hot galvanised

Master data

Item number	5015057
Type	1810
Description 1	Equipotential busbar
Manufacturer	OBO
Dimension	348mm
Material	Steel
Surface	Hot galvanised
Surface standard	DIN 267, Teil 10
Smallest sales unit	1
Unit of quantity	Piece
Weight	170 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	4,6032 kg CO2e / 1 Piece


Technical data sheet

Equipotential busbar, solid version

Item number: 5015057



Dimensions



Length	348 mm
Width	120 mm
Height	83 mm

Technical data

Quantity of flat conductor connections up to 30 mm	0
Quantity of flat conductor connections up to 40 mm	1
Quantity of cable connections up to 16 mm ² , rigid	6
Quantity of cable connections up to 25 mm ² , rigid	0
Quantity of cable connections up to 6 mm ² , rigid	0
Quantity of cable connections up to 95 mm ² , rigid	0
Quantity of round conductor connections 10 mm	0
Quantity of round conductor connections 8 mm	0
Quantity of round conductor connections 8-10 mm	1
Quantity of round conductor connections, total	1
Version for	With cover hood
Type	Fixed structure
Insulator	no
Surface of the terminal	Electrogalvanised
Surface of the contact rail	Nickel-plated
Material of the terminal	Steel
Material of the contact rail	Brass