

Technical data sheet

Twin cable gland, PG thread, light grey

Item number: 2024136



With removable polystyrene lid, as well as two connection thread sealing rings made of polyethylene.
113/13.5: with connection thread Pg 13.5, 2 half glands Pg 13.5 for cable diameter 6.5–10.5 mm.



Duroplast, Aminoplast

Master data		
Item number	2024136	
Type	113 PG13.5 LGR	
Description 1	Twin cable threaded connection	
Manufacturer	OBO	
Dimension	PG13,5	
Colour	Light grey; RAL 7035	
Material	Duroplast, Aminoplast Typ 131.5	
Smallest sales unit	5	
Unit of quantity	Piece	
Weight	3.752 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,2269 kg CO2e / 1 Piece	


Technical data sheet

Twin cable gland, PG thread, light grey

Item number: 2024136



Dimensions



Technical data

Version for	Straight
Bend protection	no
Sealing area D, max.	10.5 mm
Sealing area D, min.	6.5 mm
explosion-proof	no
Flat cable gland	no
Flame-resistant	acc. to VDE 0471/DIN 695 Part 2-1, test temperature 650°C
For Ex zone	Without
Thread	Pg 13,5
Thread type	PG
Fibre-glass reinforced	no
Halogen-free	yes
Sealing insert, multiple	no
With locknut	no
Impact-resistant	no
Protection rating	IP54
Splittable gland	no
Strain relief option	no