

Technical data sheet

Combination arrester V50, 1-pole 150 V

Item number: 5093440



- Lightning current combination arrester, type 1+2
- For lightning current equipotential bonding to VDE 0185-305 (IEC 62305)
 - Lightning current arresting capacity of 12.5 kA (10/350) per pole and up to 50 kA (10/350) in total
 - Modular, plug-in arrester with cut-off unit and visual status display
 - Locking mechanism with vibration protection and voltage keying
 - Plastic to UL 94 V-0
 - The remote signalling (FS) variants have a potential-free changeover contact for remote signalling
- Application: Lightning current equipotential bonding for buildings of class III and IV.
- * Complete = Plug-in arrester and base



PA

Polyamide

Master data		
Item number	5093440	
Type	V50-1-150	
Description 1	CombiController V50	
Description 2	1-pole	
Manufacturer	OBO	
Dimension	150V	
Material	Polyamide	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	15.4 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,622 kg CO2e / 1 Piece	


Technical data sheet

Combination arrester V50, 1-pole 150 V


Item number: 5093440



Dimensions



Technical data



Connection cross-section (min.)	1.5 mm ²
Response time	<25 ns
Response time [L-N]	25 ns
Blow-out	no
Pole version	1
Structural width in division units (division unit, 17.5 mm)	1
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Lightning surge current (10/350 µs)	12.5 kA
Lightning surge current (10/350 µs) [L-N/PE]	12.5 kA
Torque	35 Lbs
Torque	4 Nm
Installation location	Interior
Remote signalling	no
Function/defect display	Visual
Housing material surge protection components	PA UL 94 V-0
Maximum continuous voltage (L- N)	150 V
Maximum continuous voltage AC	150 V
Integrated back-up fuse	no
Short-circuit resistance for max. mains-side overcurrent protection	50 kA eff
Conductor cross-section, flexible (fine-wire), max.	35 mm ²
Conductor cross-section, flexible (fine-wire), max.	2 AWG
Conductor cross-section, flexible (fine-wire), min.	16 AWG
Conductor cross-section, flexible (fine-wire), min.	1.5 mm ²
Conductor cross-section, rigid (single-wire/multiwire), max.	2 AWG
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	16 AWG
Conductor cross-section, rigid (single-wire/multiwire), min.	1.5 mm ²

Technical data sheet

Combination arrester V50, 1-pole 150 V

Item number: 5093440



Technical data



Humidity, min.	5 %
Humidity, max.	95 %
Max. mains-side overcurrent protection	160 A gL/gG
Maximum back-up fuse	160 A
Maximum discharge current (8/20 µs)	50 kA
Maximum discharge current (8/20 µs) [L-N]	50 kA
Minimum distance	1.5 mm
Installation type	DIN rail 35 mm
Nominal discharge current (8/20 µs)	30 kA
Nominal discharge current (8/20 µs) [L-N]	30 kA
Nominal frequency	50 Hz
Nominal voltage AC (50/60 Hz)	120 V
Network form	TN
TN network form	yes
TN-C network form	yes
TN-C-S network form	yes
TN-S network form	yes
TT network form	yes
Pole number	1
Ports	One-Port SPD
Residual voltage [L-N] @ 1 kA	0.4 kV
Residual voltage [L-N] @ 12.5 kA	0.6 kV
Residual voltage [L-N] @ 5 kA	0.5 kV
Residual voltage [L-N] @ 7 kA	0.55 kV
ROHS-conformant	yes
Protection rating	IP20
Protective conductor current	< 800 µA
Protection level	≤0,8 kV
Protection level [L-N]	≤0,8
Signalling on device	Visual
SPD to EN 61643-11	Type 1+2
SPD to IEC 61643-11	Class I+II
SPD to UL 1449	Type 4
Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-40 °C
TOV voltage [L-N] – fail safe mode – 120 min.	230 V
TOV voltage [L-N] – withstand mode – 5 s	175 V
Approvals	VDE KEMA UL ÖVE