

# Technical data sheet

## Surge arrester V20, 4-pole, 550 V

Item number: 5095214



### Surge arrester, type 2

- For surge voltage protection equipotential bonding to VDE 0100-443 (IEC 60364-4-44)
- Discharge capacity to 40 kA (8/20) per pole through high-performance varistors
- Modular connectable arrester with cut-off unit and visual status display
- Locking mechanism with vibration protection and voltage keying
- Plastic to UL 94 V-0
- The remote signalling variants (FS) have a potential-free changeover contact for remote signalling

Application: Equipotential bonding in main and sub-distributions.



### Master data

|                                    |                         |
|------------------------------------|-------------------------|
| Item number                        | 5095214                 |
| Type                               | V20-4-550               |
| Description 1                      | SurgeController V20     |
| Description 2                      | 4-pole                  |
| Manufacturer                       | OBO                     |
| Dimension                          | 550V                    |
| Smallest sales unit                | 1                       |
| Unit of quantity                   | Piece                   |
| Weight                             | 49.8 kg                 |
| Weight unit                        | kg/100 pc.              |
| CO2 Footprint (GWP) Cradle-to-Gate | 2,025 kg CO2e / 1 Piece |


# Technical data sheet

## Surge arrester V20, 4-pole, 550 V


Item number: 5095214



### Dimensions



### Technical data



|                                                                     |                     |
|---------------------------------------------------------------------|---------------------|
| Arrester surge current (8/20 $\mu$ s) [total]                       | 160 kA              |
| Connection cross-section (min.)                                     | 1.5 mm <sup>2</sup> |
| Response time                                                       | <25 ns              |
| Response time [L-N]                                                 | 25 ns               |
| Blow-out                                                            | no                  |
| Pole version                                                        | 4                   |
| Structural width in division units (division unit, 17.5 mm)         | 4                   |
| Operating temperature, max.                                         | 80 °C               |
| Operating temperature, min.                                         | -40 °C              |
| Torque                                                              | 35 Lbs              |
| Torque                                                              | 4 Nm                |
| Installation location                                               | Interior            |
| Remote signalling                                                   | no                  |
| Function/defect display                                             | Visual              |
| Housing material surge protection components                        | PA UL 94 V-0        |
| Maximum continuous voltage (L-N)                                    | 550 V               |
| Maximum continuous voltage AC                                       | 550 V               |
| Integrated back-up fuse                                             | no                  |
| Short-circuit resistant                                             | yes                 |
| Short-circuit resistance for max. mains-side overcurrent protection | 50 kA eff           |
| Conductor cross-section, flexible (fine-wire), max.                 | 35 mm <sup>2</sup>  |
| Conductor cross-section, flexible (fine-wire), max.                 | 2 AWG               |
| Conductor cross-section, flexible (fine-wire), min.                 | 16 AWG              |
| Conductor cross-section, flexible (fine-wire), min.                 | 1.5 mm <sup>2</sup> |
| Conductor cross-section, rigid (single-wire/multiwire), max.        | 2 AWG               |
| Conductor cross-section, rigid (single-wire/multiwire), max.        | 35 mm <sup>2</sup>  |
| Conductor cross-section, rigid (single-wire/multiwire), min.        | 16 AWG              |
| Conductor cross-section, rigid (single-wire/multiwire), min.        | 1.5 mm <sup>2</sup> |
| Humidity, min.                                                      | 5 %                 |
| Humidity, max.                                                      | 95 %                |
| Max. mains-side overcurrent protection                              | 160 A gL/gG         |


# Technical data sheet

## Surge arrester V20, 4-pole, 550 V

Item number: 5095214



### Technical data



|                                               |                |
|-----------------------------------------------|----------------|
| Maximum back-up fuse                          | 160 A          |
| Maximum discharge current (8/20 µs)           | 40 kA          |
| Maximum discharge current (8/20 µs) [L-N]     | 40 kA          |
| Minimum distance                              | 1.5 mm         |
| Installation type                             | DIN rail 35 mm |
| Nominal discharge current (8/20 µs)           | 15 kA          |
| Nominal discharge current (8/20 µs) [L-N]     | 20 kA          |
| Nominal voltage AC (50/60 Hz)                 | 400 V          |
| Network form                                  | Other          |
| TN network form                               | yes            |
| TN-C-S network form                           | yes            |
| TN-S network form                             | yes            |
| Pole number                                   | 4              |
| Ports                                         | One-Port SPD   |
| Test class, type 2                            | yes            |
| Residual voltage [L-N] @ 1 kA                 | 1.7 kV         |
| Residual voltage [L-N] @ 5 kA                 | 2.1 kV         |
| ROHS-conformant                               | yes            |
| Protection rating                             | IP20           |
| Protective conductor current                  | < 500 µA       |
| Protection level                              | ≤2,4 kV        |
| Protection level [L-N]                        | ≤2,4           |
| Signalling on device                          | Visual         |
| SPD to EN 61643-11                            | Type 2         |
| SPD to IEC 61643-11                           | Class II       |
| SPD to UL 1449                                | Type 4         |
| Permitted temperature range, max.             | 80 °C          |
| Permitted temperature range, min.             | -40 °C         |
| TOV voltage [L-N] – fail safe mode – 120 min. | 915 V          |
| TOV voltage [L-N] – withstand mode – 5 s      | 700 V          |
| Approvals                                     | UL             |