

Technical data sheet

Surge arrester, 2-pole with audible signalling 280 V


Item number: 5096375



- Surge arrester, type 2
- Complete unit consisting of upper part and base, pre-mounted and ready for connection
 - Suitable for TN network systems
 - Plug-in upper part; upper part can be separated from base without tools
 - Incl. thermal and dynamic cut-off unit
 - With audible signalling for function monitoring, signal tone can be turned off for 24 h
 - With visual display of defects
 - High current conductivity and long service life
 - Labelled connections
- Application example: Residential buildings, single-family homes and industrial
- * Complete = cover and base



Master data		
Item number	5096375	
Type	V20-C 2+AS-280	
Description 1	SurgeController V20	
Description 2	with acoustic signalling	
Manufacturer	OBO	
Dimension	280V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	35 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	1,2815 kg CO2e / 1 Piece	



Technical data sheet

Surge arrester, 2-pole with audible signalling 280 V

Item number: 5096375



Technical data

Arrester surge current (8/20 µs) [total]	40 kA
Response time	<25 ns
Blow-out	no
Version for	2-pole with AS; 280 V
Pole version	2
Structural width in division units (division unit, 17.5 mm)	3
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Remote signalling	no
Maximum continuous voltage AC	280 V
Integrated back-up fuse	no
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Lightning protection zone LPZ	1→2
Max. mains-side overcurrent protection	125
Maximum back-up fuse	125 A
Maximum discharge current (8/20 µs)	40 kA
Installation type	DIN rail 35 mm
Nominal discharge current (8/20 µs)	20 kA
Nominal discharge current (8/20 µs) [L-N]	20 kA
Nominal voltage AC (50/60 Hz)	230 V
Network form	TN
TN network form	yes
TN-C network form	yes
Test class, type 2	yes
ROHS-conformant	yes
Protection rating	IP20
Protection level	≤1,3 kV
Signalling on device	Optical and acoustic
SPD to EN 61643-11	Type 2
SPD to IEC 61643-11	Class II
Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-40 °C