


Technical data sheet

VG housing with MCD 50-B/3

Item number: 5096874



Combination arrester, pre-installed in IP65 housing for use in TN-C networks.

VG...: Combination arrester system solution, type 1+2, according to EN 61643-11.

- LightningController MCD 50-B mounted in insulating housing IP 65, sealable housing
- Pulse current 150 kA 10/350 μ s / 50 kA (10/350) per pole, BET-tested
- Protection level < 1.7 kV
- Encapsulated, non-extinguishing spark gaps
- Suitable for TN-C network systems

Application: Industrial systems and buildings with external lightning protection of the highest Class I to IV.



Master data

Item number	5096874
Type	MCD 50-B 3-VG
Description 1	CoordinatedLightningController
Description 2	set type 1 arrester in housing
Manufacturer	OBO
Dimension	255V
Smallest sales unit	1
Unit of quantity	Piece
Weight	315 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	6,7355 kg CO2e / 1 Piece



Technical data sheet

VG housing with MCD 50-B/3




Item number: 5096874

Dimensions



Length	300 mm
Width	300 mm
Height	170 mm

Technical data



Arrester surge current (8/20 μ s) [total]	150 kA
Response time	<100 ns
Blow-out	no
Pole version	3
Structural width in division units (division unit, 17.5 mm)	6
Operating temperature, max.	85 °C
Operating temperature, min.	-40 °C
Lightning surge current (10/350 μ s)	50 kA
Lightning surge current (10/350)	150 kA
Remote signalling	yes
Follow current quenching capacity left	10 kA
Maximum continuous voltage AC	255 V
Short-circuit resistance	10 kA
Short-circuit resistance for max. mains-side overcurrent protection	10 kA
Conductor cross-section, rigid (single-wire/multiwire), max.	50 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	10 mm ²
Lightning protection zone LPZ	0→2
Max. mains-side overcurrent protection	500
Maximum back-up fuse	500 A
Installation type	Pre-mounted in the housing
Nominal discharge current (8/20 μ s)	50 kA
Nominal voltage AC (50/60 Hz)	230 V
Network form	TN-C
TN network form	yes
TN-C network form	yes


Technical data sheet

VG housing with MCD 50-B/3

Item number: 5096874



Technical data



OBO_Nominal load current (input/output terminal)

125 A

Test class, type 1

yes

Test class, type 2

yes

ROHS-conformant

yes

Protection rating

IP54

Protection level

≤1,7 kV

Protection level [L-N]

≤1,7

Signalling on device

None

SPD to EN 61643-11

Type 1+2

SPD to IEC 61643-11

Class I+II

Permitted temperature range, max.

85 °C

Permitted temperature range, min.

-40 °C