

Technical data sheet

Decoupling inductivity

Item number: 5096970



Decoupling inductance

- Compact design in a 35 mm housing
- Two connection options for input and output
- Rated load current 63 A
- Nominal inductance 5 µH

Application example: In combination with MC 50-B VDE and V 20-C with cable lengths of less than 5 m.



Master data		
Item number	5096970	
Type	LC 63	
Description 1	LightningCoordinator	
Description 2	decoupling inductivity	
Manufacturer	OBO	
Dimension	500V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	43.5 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	125,6477 kg CO2e / 1 Piece	


Technical data sheet

Decoupling inductivity

Item number: 5096970



Dimensions



Technical data

	Blow-out	no
	Version for	63 A
	Pole version	1
	Structural width in division units (division unit, 17.5 mm)	2
	Operating temperature, max.	85 °C
	Operating temperature, min.	-40 °C
	Remote signalling	no
	Maximum continuous voltage AC	500 V
	Inductivity	5 µH
	Conductor cross-section, rigid (single-wire/multiwire), max.	50 mm²
	Conductor cross-section, rigid (single-wire/multiwire), min.	10 mm²
	Max. mains-side overcurrent protection	63
	Maximum back-up fuse	63 A
	Nominal voltage AC (50/60 Hz)	0 V
	OBO_Nominal load current (input/ output terminal)	63 A
	ROHS-conformant	yes
	Protection rating	IP20
	Signalling on device	None
	Permitted temperature range, max.	85 °C
	Permitted temperature range, min.	-40 °C