

Technical data sheet

Surge arrester V10 1-pole + NPE 280 V

Item number: 5093418



- Surge arrester, type 2+3
- Complete unit consisting of upper part and base, pre-mounted and ready for connection
 - Suitable for TN-S and TT network systems
 - Incl. thermal and dynamic cut-off unit
 - With visual display of defects
 - High current conductivity and long service life
 - Labelled connections

Application example: Residential buildings, single-family homes



Master data		
Item number	5093418	
Type	V10-C 1+NPE-280	
Description 1	SurgeController V10	
Description 2	single pole version with NPE	
Manufacturer	OBO	
Dimension	280V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	23.5 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	1,1554 kg CO2e / 1 Piece	

Dimensions		


Technical data sheet

Surge arrester V10 1-pole + NPE 280 V

Item number: 5093418



Technical data



Arrester surge current (8/20 µs) [total]	20 kA
Response time	<25 ns
Blow-out	no
Pole version	1+N/PE
Structural width in division units (division unit, 17.5 mm)	2
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Remote signalling	no
Maximum continuous voltage (N-PE)	255 V
Maximum continuous voltage AC	280 V
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Lightning protection zone LPZ	1→3
Max. mains-side overcurrent protection	125
Maximum back-up fuse	125 A
Maximum discharge current (8/20 µs)	20 kA
Maximum discharge current (8/20 µs) [L-N]	20 kA
Maximum discharge current (8/20 µs) [N-PE]	50 kA
Installation type	DIN rail 35 mm
Nominal discharge current (8/20 µs)	10 kA
Nominal discharge current (8/20 µs) [L-N]	10 kA
Nominal discharge current (8/20 µs) [N-PE]	30 kA
Nominal voltage AC (50/60 Hz)	230 V
Network form	Other
TN network form	yes
TN-C-S network form	yes
TN-S network form	yes
TT network form	yes
Test class, type 2	yes
ROHS-conformant	Exempt
Protection rating	IP20
Protection level	≤1,1 kV
Protection level [N-PE]	1.2 kV
Signalling on device	Visual
SPD to EN 61643-11	Type 2+3
SPD to IEC 61643-11	Class II+III
Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-40 °C