

Technical data sheet

Medium and fine protection FRD 2 for two-core systems 24 V

Item number: 5098727



Surge protection for use in measurement and control technology

- Medium and fine protection
- Standard design for double core systems
- Two-stage protection circuit
- With installation-friendly, screwless connection terminals
- In space-saving 17.5 mm grid
- With ohmic decoupling in the longitudinal branch

Application: Universal use on any 35 mm DIN profile rail in every commercially available distributor housing.



Master data		
Item number	5098727	
Type	FRD 2-24	
Description 1	Lightning barrier	
Description 2	with decoupling resistance	
Manufacturer	OBO	
Dimension	24V AC	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	5.1 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,3121 kg CO2e / 1 Piece	


Technical data sheet

Medium and fine protection FRD 2 for two-core systems 24 V


Item number: 5098727



Dimensions



Technical data



Arrestor monitoring	no
Connection cross-section, flexible, max.	2.5 mm ²
Connection cross-section, flexible, min.	0.14 mm ²
Connection cross-section, multi-wire, max.	2.5 mm ²
Connection cross-section, multi-wire, min.	0.14 mm ²
Connection cross-section, rigid, max.	2.5 mm ²
Connection cross-section, rigid, min.	0.14 mm ²
Number of poles	2
Insertion loss	3 dB @ 1 MHz dB
Earthing via:	Terminal
Explosion-tested version	no
Telecommunications contact	no
Total discharge current (8/20)	5 kA
Maximum continuous voltage AC	19 V
Maximum continuous voltage DC	28 V
Insulation resistance	>10 MΩ
Capacity (wire-wire)	<10 nF
Capacity (wire-earth)	<10 nF
Kategorie	Type 2+3 / C2+C1
Lightning protection zone LPZ	1→3
Mounting type	DIN rail 35 mm
Nominal discharge current (8/20 μs)	2.5 kA
Nominal load current AC	0.14 A
Nominal load current DC	0.2 A
Nominal voltage	24 V
Testing standard	IEC 61643-21
ROHS-conformant	yes
Shielding connection available	no
Protection rating	IP20
Protection level wire-wire	<120 V
Protection level wire-earth	<60 V
Series resistance per wire	15 Ω ± 10 %

Technical data sheet

Medium and fine protection FRD 2 for two-core systems 24 V

Item number: 5098727



Technical data		
	SPD to IEC 61643-21	Class II+III / C2+C1
	Plug-in system	Terminal
	Impulse durability wire-wire	C2: 5 kV / 2,5 kA (8/20µs)
	Impulse durability wire-earth	C2: 5 kV / 2,5 kA (8/20µs)
	Division unit TE (17.5 mm)	1
	Permitted temperature range, max.	80 °C
	Permitted temperature range, min.	-40 °C