

Technical data sheet

Combination arrester V25, 1-pole + NPE 280 V

Item number: 5094457



Combination arrester, lightning and surge arrester type 1+2

- Complete unit consisting of upper part and base, pre-mounted and ready for connection
- Universally suitable for TN-S and TT systems
- Plug-in arrester with dynamic cut-off unit
- Visual function display
- Voltage protection level < 0.9 kV
- Encapsulated, non-extinguishing zinc oxide varistor arrester for use in standard distributor housings
- Labelled connections

Application example: Buildings with open-wire power supply or for setting up lightning protection equipotential bonding in residential buildings.
* Complete = Plug-in arrester and base



Type 1+2 LPZ 0→2

Master data		
Item number	5094457	
Type	V25-B+C 1+NPE	
Description 1	CombiController V25	
Description 2	1+1 version	
Manufacturer	OBO	
Dimension	280V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	24.61 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	1,0825 kg CO2e / 1 Piece	

Dimensions		


Technical data sheet

Combination arrester V25, 1-pole + NPE 280 V

Item number: 5094457



Technical data



Arrester surge current (8/20 µs) [total]	60 kA
Response time	<25 ns
Blow-out	no
Version for	1-pole complete with NPE
Pole version	1+N/PE
Structural width in division units (division unit, 17.5 mm)	2
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Lightning surge current (10/350 µs)	7 kA
Lightning surge current (10/350 µs) [N/PE]	25 kA
Lightning surge current (10/350 µs)	14 kA
Remote signalling	no
Follow current quenching capacity I _{eff}	25 kA
Combined voltage protection level [L-PE]	1200 kV
Maximum continuous voltage AC	280 V
Maximum continuous voltage DC	200 V
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Lightning protection zone LPZ	0→2
Max. mains-side overcurrent protection	160
Maximum back-up fuse	160 A
Maximum discharge current (8/20 µs)	50 kA
Nominal discharge current (8/20 µs)	30 kA
Nominal discharge current (8/20 µs) [L-N]	30 kA
Nominal discharge current (8/20 µs) [N-PE]	30 kA
Nominal voltage AC (50/60 Hz)	230 V
Network form	Other
TN network form	yes
TN-C-S network form	yes
TN-S network form	yes
TT network form	yes
Pole number	1
ROHS-conformant	Exempt
Protection rating	IP20
Protection level	≤0,9 kV
Protection level [L-N]	≤900
Signalling on device	Visual
SPD to EN 61643-11	Type 1+2
SPD to IEC 61643-11	Class I+II
Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-40 °C