


Technical data sheet

Heavy-duty cable tray SGR 55 FT

Item number: 6000451



Mesh cable tray made of spot-welded steel wire of side height 55 mm.
The grid width is 50 x 100 mm.
Magnetic shield insulation without cover 15 dB, with cover 25 dB.



St

Steel

FT

Hot-dip galvanised

Master data

Item number	6000451
Type	SGR 55 400 FT
Description 1	Mesh cable tray SGR
Manufacturer	OBO
Dimension	55x400x3000
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	3
Unit of quantity	Metre
Weight	372.667 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	7,6943 kg CO2e / 1 Meter


Technical data sheet

Heavy-duty cable tray SGR 55 FT

Item number: 6000451



Dimensions




Length	3,000 mm
Width	400 mm
Width	15.75 in
Height	55 mm
Height	2.17 in
Dimension B	400 mm

Technical data

Connector version	Without connectors
Mounting system fastening type	Ceiling Wall
Usable cross-section	175 cm ²
Usable cross-section	17500 mm ²
Profile shape	U-shaped
ROHS-conformant	yes
Load test type according to IEC 61537	Type II
Type of connector, cable support system	Screwed

Loads

Insertable support spacings, min.	1 m
Insertable support spacings, max.	3 m
Support spacing 1.0 m	2.3 kN/m
Support spacing 1.5 m	1.3 kN/m
Support spacing 2.0 m	0.75 kN/m
Support spacing 2.5 m	0.45 kN/m
Support spacing 3.0 m	0.4 kN/m



Load diagram, mesh cable tray, type SGR 55

- 1 Permitted cable tray/ladder load in kN/m without man load
 - 2 Support width in m
 - 3 Rail bend in mm at permitted kN/m
 - 4 Load scheme during testing
- Load curve with cable tray/ladder width in mm
- Strut bend curve according to support width