

Technical data sheet

Plug-in arrester V20 550 V

Item number: 5095372



Surge arrester, type 2

- For surge protection equipotential bonding to VDE 0100-443 (IEC 60364-4-44)
- Discharge capacity to 40 kA (8/20) per pole through high-performance varistors
- Modular, plug-in arrester with dynamic cut-off unit and visual status display
- Locking mechanism with vibration protection and voltage keying
- Plastic (UL 94 V-0)



Master data		
Item number	5095372	
Type	V20-0-550	
Description 1	SurgeController V20	
Description 2	plug-in arrester	
Manufacturer	OBO	
Dimension	550V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	6.36 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,1548 kg CO2e / 1 Piece	


Technical data sheet

Plug-in arrester V20 550 V

Item number: 5095372



Dimensions



Technical data



Response time [L-N]	25 ns
Response time [N-PE]	100 ns
Blow-out	no
Pole version	1
Structural width in division units (division unit, 17.5 mm)	1
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Installation location	Interior
Remote signalling	no
Function/defect display	Visual
Housing material surge protection components	PA UL 94 V-0
Maximum continuous voltage (L- N)	550 V
Maximum continuous voltage AC	550 V
Integrated back-up fuse	no
Short-circuit resistant	yes
Short-circuit resistance for max. mains-side overcurrent protection	50 kA eff
Humidity, min.	5 %
Humidity, max.	95 %
Maximum discharge current (8/20 µs)	40 kA
Maximum discharge current (8/20 µs) [L-N]	40 kA
Minimum distance	1.5 mm
Installation type	On basic element
Nominal discharge current (8/20 µs)	20 kA
Nominal discharge current (8/20 µs) [L-N]	20 kA
Nominal voltage AC (50/60 Hz)	400 V
Network form	Other
Pole number	1
Ports	One-Port SPD
Test class, type 2	yes
ROHS-conformant	yes
Protection rating	IP20
Protective conductor current	< 500 µA
Protection level	≤2,4 kV
Protection level [L-N]	≤2,4
Signalling on device	Visual

Technical data sheet

Plug-in arrester V20 550 V

Item number: 5095372



Technical data



SPD to EN 61643-11	Type 2
SPD to IEC 61643-11	Class II
SPD to UL 1449	Type 4
Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-40 °C
Approvals	UL