


# Technical data sheet

## Beam clamp, vertical BFK 166 FT

Item number: 6003888



Beam clamp for clamping on the steel girder.  
The cable support system attached to the beam clamp runs vertically.



|    |                    |
|----|--------------------|
| St | Steel              |
| FT | Hot-dip galvanised |

### Master data

|                                    |                                |
|------------------------------------|--------------------------------|
| Item number                        | 6003888                        |
| Type                               | BFK 166 58 20 FT               |
| Description 1                      | Clamping piece                 |
| Description 2                      | for max. supp. thickness 20 mm |
| Manufacturer                       | OBO                            |
| Colour                             | zinc                           |
| Material                           | Steel                          |
| Surface                            | Hot-dip galvanised             |
| Surface standard                   | DIN EN ISO 1461                |
| Smallest sales unit                | 10                             |
| Unit of quantity                   | Piece                          |
| Weight                             | 45 kg                          |
| Weight unit                        | kg/100 pc.                     |
| CO2 Footprint (GWP) Cradle-to-Gate | 1,0369 kg CO2e / 1 Piece       |


# Technical data sheet

## Beam clamp, vertical BFK 166 FT

Item number: 6003888



### Dimensions



|              |        |
|--------------|--------|
| Width        | 166 mm |
| Height       | 20 mm  |
| Dimension B  | 166 mm |
| Dimension b  | 133 mm |
| Dimension B1 | 133 mm |

### Technical data

|                             |               |
|-----------------------------|---------------|
| Version for                 | Miscellaneous |
| Suitable for profile shapes | C profile     |
| ROHS-conformant             | yes           |