

Technical data sheet

Base, MultiBase + NPE with remote signalling

Item number: 5096671




- Suitable for V 25-B+C, V 20-C and V10-C
- Pre-mounted and ready for connection
- Multifunction terminals for easy connection to series-mounted devices
- Upper parts can be rotated through 180 degrees
- With remote signalling, potential-free NO contact, for function monitoring
- 3+1 protection circuit for TN-S and TT network systems



Master data

Item number	5096671
Type	MB 3+NPE+FS
Description 1	MultiBase
Description 2	3-pole + NPE w. signal contact
Manufacturer	OBO
Dimension	3+NPE+FS
Smallest sales unit	1
Unit of quantity	Piece
Weight	21 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,1679 kg CO2e / 1 Piece

Dimensions



Technical data sheet

Base, MultiBase + NPE with remote signalling

Item number: 5096671



Technical data

Version for	3+NPE
Pole version	3+N/PE
Structural width in division units (division unit, 17.5 mm)	4
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Remote signalling	yes
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Installation type	DIN rail 35 mm
Network form	Other
ROHS-conformant	Exempt
Protection rating	IP20
Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-40 °C