

Technical data sheet

Medium and fine protection FLD 2 for two-core systems 12 V

Item number: 5098808



Surge protection for use in measurement and control technology

- Medium and fine protection
- Standard design for single core systems
- Two-stage protection circuit
- With installation-friendly, screwless connection terminals
- In space-saving 17.5 mm grid
- With inductive decoupling in the longitudinal branch

Application: Universal use on any 35 mm DIN profile rail in every commercially available distributor housing.



Master data		
Item number	5098808	
Type	FLD 2-12	
Description 1	Lightning barrier	
Description 2	with decoupling inductivity	
Manufacturer	OBO	
Dimension	12V AC	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	5.1 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,1438 kg CO2e / 1 Piece	


Technical data sheet

Medium and fine protection FLD 2 for two-core systems 12 V

Item number: 5098808



Dimensions



Technical data

	Connection cross-section, flexible, max.	2.5 mm ²
	Connection cross-section, flexible, min.	0.14 mm ²
	Connection cross-section, multi-wire, max.	2.5 mm ²
	Connection cross-section, multi-wire, min.	0.14 mm ²
	Connection cross-section, rigid, max.	2.5 mm ²
	Connection cross-section, rigid, min.	0.14 mm ²
	Number of poles	2
	Insertion loss	3dB @ 150 kHz dB
	Earthing via:	Terminal
	Explosion-tested version	no
	Telecommunications contact	no
	Total discharge current (8/20)	1 kA
	Maximum continuous voltage AC	9 V
	Maximum continuous voltage DC	13 V
	Insulation resistance	>1MΩ
	Capacity (wire-wire)	<10 nF
	Capacity (wire-earth)	<10 nF
	Kategorie	Type 2+3 / C2+C1
	Lightning protection zone LPZ	1→3
	Mounting type	DIN rail 35 mm
	Nominal discharge current (8/20 μs)	0.5 kA
	Nominal load current AC	0.7 A
	Nominal load current DC	1 A
	Testing standard	IEC 61643-21
	ROHS-conformant	yes
	Shielding connection available	no
	Protection rating	IP20
	Protection level wire-wire	<60 V
	Protection level wire-earth	<30 V
	Series inductivity per wire	120 μH ± 10 %
	SPD to IEC 61643-21	Class II+III / C2+C1
	Plug-in system	Terminal


Technical data sheet

Medium and fine protection FLD 2 for two-core systems 12 V

Item number: 5098808



Technical data



Impulse durability wire-wire	C1: 1 kV / 0,5 kA (8/20µs)
Impulse durability wire-earth	C1: 1 kV / 0,5 kA (8/20µs)
Division unit TE (17.5 mm)	1
Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-40 °C
Approvals	UL