


Technical data sheet

Cable tray, marine standard A2

Item number: 6045836



Cable tray for use in ship construction, produced according to the marine standard VG 88900-1.



A2 Stainless steel

2B Bright, treated

Master data

Item number	6045836
Type	MKR 15 125 A2
Description 1	Cable tray marine standard
Description 2	Material thickness 1.25mm
Manufacturer	OBO
Dimension	15x125x2000
Colour	stainless steel
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	2
Unit of quantity	Metre
Weight	113.4 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	10,5972 kg CO2e / 1 Meter


Technical data sheet

Cable tray, marine standard A2

Item number: 6045836



Dimensions



Dimension	15 X 125
Length	2,000 mm
Width	125 mm
Height	15 mm
Plate thickness	1.25 mm
Dimension B	125 mm

Technical data

Connector version	Without connectors
Walkable	no
Maintain electrical functions	no
With cover	no
Mounting perforation in base	yes
NATO hole pattern	yes
ROHS-conformant	yes
Rustproof steel, pickled	yes
Side perforation	no
Wide-span version	no
Load test type according to IEC 61537	Type II
Type of connector, cable support system	Screwed

Loads

Support spacing 1.0 m	0.35 kN/m
Support spacing 1.5 m	0.15 kN/m