

Technical data sheet

Cable tray MKS 35 FS

Item number: 6053637



MKS 35 = Medium duty cable tray system with a side height of 35 mm.
Magnetic shield insulation without cover 20 dB, with cover 50 dB.



St	Steel
FS	Strip galvanised

Master data

Item number	6053637
Type	MKS 330 FS
Description 1	Cable tray MKS
Description 2	perforated
Manufacturer	OBO
Dimension	35x300x3000
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	3
Unit of quantity	Metre
Weight	269.433 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	7,1067 kg CO2e / 1 Meter


Technical data sheet

Cable tray MKS 35 FS

Item number: 6053637



Dimensions



Dimension	35 x 300
Length	3,000 mm
Length	10 ft
Width	300 mm
Width	12 in
Height	35 mm
Plate thickness	1 mm
Dimension B	300 mm

Technical data

Mounting system fastening type	Floor Ceiling Wall
Walkable	no
Base perforation	1
Maintain electrical functions	no
With cover	no
Mounting perforation in base	yes
Usable cross-section	103 cm ²
Usable cross-section	10300 mm ²
ROHS-conformant	yes
Rustproof steel, pickled	no
Side perforation	yes
Wide-span version	no
Load test type according to IEC 61537	Type II
Type of connector, cable support system	Screwed

Technical data sheet


Cable tray MKS 35 FS

Item number: 6053637



Loads

Insertable support spacings, min.	1 m
Insertable support spacings, max.	3 m
Support spacing 1.0 m	1.1 kN/m
Support spacing 1.5 m	0.5 kN/m
Support spacing 2.0 m	0.3 kN/m
Support spacing 2.5 m	0.3 kN/m
Support spacing 3.0 m	0.2 kN/m



Load diagram, cable tray, type MKS 35

- 1 Permitted cable tray/ladder load in kN/m without man load
- 2 Support width in m
- 3 Rail bend in mm at permitted kN/m
- 4 Load scheme during testing
- Load curve with cable tray/ladder width in mm
- Strut bend curve according to support width