


Technical data sheet

Cable tray MKSU 60 FT

Item number: 6063150



Medium-duty unperforated cable tray for horizontal routing of cables and lines. According to EN 61537. Can be used in indoor areas. Screw connection. Suitable for direct and elevated floor mounting as well as for wall and ceiling mounting on support system. With connector perforation on end of cable tray. Magnetic shield insulation without cover 20 dB, with cover 50 dB. Matching cover with turn buckle: Type AZDMD 50



St

Steel

FS

Strip galvanised

Master data

Item number	6063150
Type	MKSU 605 FS
Description 1	Cable tray MKSU
Description 2	unperforated, connector holes
Manufacturer	OBO
Dimension	60x50x3000
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	3
Unit of quantity	Metre
Weight	142.667 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	3,7616 kg CO2e / 1 Meter


Technical data sheet

Cable tray MKSU 60 FT

Item number: 6063150



Dimensions



Dimension	60x50
Length	3,000 mm
Width	50 mm
Height	60 mm
Plate thickness	1 mm
Dimension B	50 mm
Dimension H	60 mm

Technical data

Connector version	Without connectors
Mounting system fastening type	Floor Ceiling Wall
Maintain electrical functions	no
Mounting perforation in base	no
Usable cross-section	30 cm ²
Usable cross-section	3000 mm ²
ROHS-conformant	yes
Rustproof steel, pickled	no
Side perforation	no
Wide-span version	no
Load test type according to IEC 61537	Type II
Type of connector, cable support system	Screwed