


Technical data sheet

Heavy-duty cable tray SGR 55 G

Item number: 6005472



Mesh cable tray made of spot-welded steel wire of side height 55 mm.
The grid dimension is 50 x 100 mm.

Stainless steel version on request.
Magnetic shield insulation without cover 15 dB, with cover 25 dB.



- St** Steel
- G** Electrogalvanised

Master data

Item number	6005472
Type	SGR 55 150 G
Description 1	Mesh cable tray SGR
Manufacturer	OBO
Dimension	55x150x3000
Colour	zinc
Material	Steel
Surface	Electrogalvanised
Surface standard	EN ISO 19598 / EN ISO 4042
Smallest sales unit	3
Unit of quantity	Metre
Weight	199 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	3,8649 kg CO2e / 1 Meter



Technical data sheet

Heavy-duty cable tray SGR 55 G

Item number: 6005472



Dimensions



Length	3,000 mm
Width	150 mm
Width	5.91 in
Height	55 mm
Height	2.17 in
Dimension B	150 mm

Technical data

Connector version	Without connectors
Mounting system fastening type	Ceiling Wall
Maintain electrical functions	no
Usable cross-section	63 cm ²
Usable cross-section	6300 mm ²
Profile shape	U-shaped
ROHS-conformant	yes
Rustproof steel, pickled	no
Wide-span version	no
Load test type according to IEC 61537	Type II
Type of connector, cable support system	Screwed

Technical data sheet


Heavy-duty cable tray SGR 55 G

Item number: 6005472



Loads

Insertable support spacings, min.	1 m
Insertable support spacings, max.	3 m
Support spacing 1.0 m	2 kN/m
Support spacing 1.5 m	1.15 kN/m
Support spacing 2.0 m	0.75 kN/m
Support spacing 3.0 m	0.4 kN/m



Load diagram, mesh cable tray, type SGR 55

- 1 Permitted cable tray/ladder load in kN/m without man load
- 2 Support width in m
- 3 Rail bend in mm at permitted kN/m
- 4 Load scheme during testing
- Load curve with cable tray/ladder width in mm
- Strut bend curve according to support width