

# Technical data sheet

## SLL 60 medium-duty vertical ladder, 6 m, FS

Item number: 6010626



Vertical ladder with a side height of 60 mm with riveted C profile rungs, open in upwards direction.  
Fastening takes place directly on the wall or using the wall brackets, type WB 30/75. The slot dimension of the rung is 18 mm and the appropriate clamp clip is type 2056U.



|    |                  |
|----|------------------|
| St | Steel            |
| FS | Strip galvanised |

### Master data

|                                    |                             |
|------------------------------------|-----------------------------|
| Item number                        | 6010626                     |
| Type                               | SLL 650 CPS 4 FS            |
| Description 1                      | Medium duty vertical ladder |
| Description 2                      | with CPS rung               |
| Manufacturer                       | OBO                         |
| Dimension                          | 60x500x6000                 |
| Colour                             | zinc                        |
| Material                           | Steel                       |
| Surface                            | Strip galvanised            |
| Surface standard                   | DIN EN 10346                |
| Smallest sales unit                | 6                           |
| Unit of quantity                   | Metre                       |
| Weight                             | 353.267 kg                  |
| Weight unit                        | kg/100 m                    |
| CO2 Footprint (GWP) Cradle-to-Gate | 8,3672 kg CO2e / 1 Meter    |


# Technical data sheet

## SLL 60 medium-duty vertical ladder, 6 m, FS

Item number: 6010626



### Dimensions



|                     |          |
|---------------------|----------|
| Length              | 6,000 mm |
| Width               | 500 mm   |
| Height              | 60 mm    |
| Dimension B         | 500 mm   |
| Rung slot dimension | 18.00    |

### Technical data

|                               |                     |
|-------------------------------|---------------------|
| Side wall version             | Flat profile        |
| Version of the rungs          | Profile perforated  |
| Maintain electrical functions | no                  |
| Usable cross-section          | 190 cm <sup>2</sup> |
| ROHS-conformant               | yes                 |
| Rustproof steel, pickled      | no                  |
| Side perforation              | yes                 |
| Rung distance                 | 600 mm              |
| Rail thickness                | 1.5 mm              |