

Technical data sheet

Mesh cable tray connector, long DD

Item number: 6016684



Long mesh cable tray connection for screwless straight connection of mesh cable trays.
Two straight connectors, type GRV 245, are used for each connection point.

Can be used from a mesh cable tray width of 100 mm.

The FS variant is used to connect electrogalvanised mesh cable trays, the DD variant to connect hot/hot-dip galvanised mesh cable trays and the VA variant to connect stainless steel mesh cable trays.



St

Steel

DD

Strip galvanised zinc/aluminium, Double Dip

Master data

Item number	6016684
Type	GRV 245 DD
Description 1	Quick connector
Description 2	for mesh cable tray, long type
Manufacturer	OBO
Dimension	L245mm
Colour	zinc
Material	Steel
Surface	Strip galvanised zinc/aluminium, Double Dip
Surface standard	DIN EN 10346
Smallest sales unit	20
Unit of quantity	Piece
Weight	13.5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,4137 kg CO2e / 1 Piece


Technical data sheet

Mesh cable tray connector, long DD

Item number: 6016684



Dimensions



Dimension	245 x 30
Length	245 mm
Width	30 mm
Width	1.18 in
Height	14 mm
Height	0.55 in
Plate thickness	2 mm

Technical data

Version for	Straight connector
Maintain electrical functions	no
Suitable for mesh cable tray	yes
Suitable for cable ladder	no
Suitable for cable tray	no
Adjustable connector, horizontal	no
Articulated connector, vertical	no
ROHS-conformant	yes
Rustproof steel, pickled	no
Connection type	Screwless connector