

Technical data sheet

Flush-mount unit for data technology, type C

Item number: 6119492



Installation unit to accommodate two type C data technology modules, suitable for installation in Rapid 80 device installation trunking systems and ISS service poles. The type C data technology support is suitable for accepting the following data connection modules: BTR (Keystone design): Cat. 6A module and UAE module; Corning: modules with Keystone seat; CobiNet: CobiDat KS module; Dätwyler: KS-T, KS-TS, MS-K and KU-T; ECU: E-Stone; Harting: Prelink Keystone Cat. 6A; Fixlink Keystone Cat. 6A; Komos: KDM 500 module; Leoni Kerpen: MegaLine Keystone Cat. 6A; OBO: Type ASM-C6A and ASM-C6A G; R&M: Cat. 6A with Keystone fastening; Rutenbeck: UM and UMflex; SETEC: UKJ and XKJ; Telegärtner: AMJ and UMJ.

Installation unit, consisting of:

- Mounting support, single, type 71MT1 45
 - Data technology support, straight outlet, type DTG-2C, colour: see table
 - Cover frame AR45, single, without labelling panel, colour: pure white
- For installation in Rapid 80 device installation trunking and ISS service poles.

PC Polycarbonate

Master data

Item number	6119492
Type	DTE-RW G2C1
Description 1	Inst.unit, data technology
Description 2	f.2 connection modules type C
Manufacturer	OBO
Dimension	84x84x59mm
Colour	Pure white; RAL 9010
Material	Polycarbonate
Smallest sales unit	1
Unit of quantity	Piece
Weight	5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,4006 kg CO2e / 1 Piece


Technical data sheet

Flush-mount unit for data technology, type C

Item number: 6119492



Dimensions



Length	84 mm
Width	84 mm

Technical data

Surface version	Matt
Labelling panel	With labelling panel
Halogen-free	yes
Hinged cover	no
Lamp-wire connector	no
With printed label	no
With dust protection	yes
Mounting type	Device installation duct
ROHS-conformant	yes
Protection rating	IP20
Depth	24.3 mm
Support ring	no
Transparent	no
Use	Modular jack
Strain relief option	no
Combination	Basic element with full cover plate