

# Technical data sheet

End piece, trunking type WDK 40060

Item number: 6021492



End piece to close the WDK trunking.  
The end pieces are pushed onto the trunking and kept in place by the spring action.



**PVC** Polyvinylchloride

## Master data

|                                    |                         |
|------------------------------------|-------------------------|
| Item number                        | 6021492                 |
| Type                               | WDK HE40060GR           |
| Description 1                      | End piece               |
| Manufacturer                       | OBO                     |
| Dimension                          | 40x60mm                 |
| Colour                             | Stone grey; RAL 7030    |
| Material                           | Polyvinylchloride       |
| Smallest sales unit                | 10                      |
| Unit of quantity                   | Piece                   |
| Weight                             | 1.144 kg                |
| Weight unit                        | kg/100 pc.              |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,055 kg CO2e / 1 Piece |


# Technical data sheet

End piece, trunking type WDK 40060

Item number: 6021492



## Dimensions



|             |         |
|-------------|---------|
| Length      | 27.5 mm |
| Width       | 60 mm   |
| Height      | 40 mm   |
| Dimension a | 60 mm   |
| Dimension b | 40 mm   |
| Dimension H | 60 mm   |

## Technical data

|                                   |            |
|-----------------------------------|------------|
| Version for                       | Left/right |
| Fastening type                    | Lockable   |
| Maintain electrical functions     | no         |
| Halogen-free                      | no         |
| ROHS-conformant                   | yes        |
| Protection rating                 | IP30       |
| Protective film                   | no         |
| Protection rating IK code         | IK04       |
| Permitted temperature range, max. | 60 °C      |
| Permitted temperature range, min. | -5 °C      |