

# Technical data sheet

## LG 60 cable ladder, 6 m VSF

Item number: 6207527



Cable ladder for the horizontal routing of cables. Can be used as a standard support structure for the maintenance of electrical functionality according to DIN 4102 Part 12. Maintenance of electrical function classes E30 to E90. With riveted C profile rung, open in an upward direction.

E30 E60 E90

St Steel

FT Hot-dip galvanised

### Master data

|                                    |                              |
|------------------------------------|------------------------------|
| Item number                        | 6207527                      |
| Type                               | LG 630 VSF 6 FT              |
| Description 1                      | Cable ladder function maint. |
| Description 2                      | rungs distance 150 mm        |
| Manufacturer                       | OBO                          |
| Dimension                          | 60x300x6000                  |
| Colour                             | zinc                         |
| Material                           | Steel                        |
| Surface                            | Hot-dip galvanised           |
| Surface standard                   | DIN EN ISO 1461              |
| Smallest sales unit                | 6                            |
| Unit of quantity                   | Metre                        |
| Weight                             | 379.166 kg                   |
| Weight unit                        | kg/100 m                     |
| CO2 Footprint (GWP) Cradle-to-Gate | 8,329 kg CO2e / 1 Meter      |


# Technical data sheet

LG 60 cable ladder, 6 m VSF

Item number: 6207527



## Dimensions



|                     |          |
|---------------------|----------|
| Length              | 6,000 mm |
| Width               | 300 mm   |
| Height              | 60 mm    |
| Dimension B         | 300 mm   |
| Rung slot dimension | 17.00    |

## Technical data

|                               |                       |
|-------------------------------|-----------------------|
| Version of the rungs          | Profile perforated    |
| Side rail version             | Profile (open)        |
| Fastening of rung             | Blind riveted         |
| Maintain electrical functions | yes                   |
| Usable cross-section          | 148 cm <sup>2</sup>   |
| Usable cross-section          | 14800 mm <sup>2</sup> |
| ROHS-conformant               | yes                   |
| Rustproof steel, pickled      | no                    |
| Side perforation              | yes                   |
| Rung distance                 | 150 mm                |
| Wide-span version             | no                    |
| Rail thickness                | 1.5 mm                |