


Technical data sheet

Multifunctional connector FS

Item number: 6225714



Multifunctional connector for joining cable ladders with a side height of 60 mm. Symmetrical and asymmetrical reductions, infinitely-adjustable bends between 0–60° and add-on tees can be created.



St	Steel
FS	Strip galvanised

Master data

Item number	6225714
Type	LMFV 640 FS
Description 1	Multifunctional connector
Description 2	for cable ladder
Manufacturer	OBO
Dimension	60x400
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	136.2 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	5,2494 kg CO2e / 1 Piece


Technical data sheet

Multifunctional connector FS

Item number: 6225714



Dimensions



Length	604 mm
Width	400 mm
Height	60 mm
Plate thickness	1.5 mm
Dimension B	400 mm

Technical data

Version for	Straight and angle connector
Maintain electrical functions	no
Suitable for mesh cable tray	no
Suitable for cable ladder	yes
Suitable for cable tray	no
Suitable for cable support system width, max.	400 mm
Suitable for cable support system width, min.	400 mm
Suitable for cable tray system height	60 mm
Adjustable connector, horizontal	no
Articulated connector, vertical	no
ROHS-conformant	yes
Rustproof steel, pickled	no
Connection type	Screw connector