

# Technical data sheet

## Coupling KUPP

Item number: 6288680



Coupling for connecting the trunking bases. This creates the equipotential bonding between the trunking bases.

The scope of delivery of a coupling includes 2 connection plates.



**A2** Stainless steel

### Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 6288680                  |
| Type                               | KUPP                     |
| Description 1                      | Coupling                 |
| Description 2                      | for desk trunking        |
| Manufacturer                       | OBO                      |
| Dimension                          | 133x105                  |
| Colour                             | stainless steel          |
| Material                           | Stainless steel 1.4301   |
| Smallest sales unit                | 1                        |
| Unit of quantity                   | Piece                    |
| Weight                             | 14.8 kg                  |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 1,1155 kg CO2e / 1 Piece |


# Technical data sheet

## Coupling KUPP

Item number: 6288680



### Dimensions



|             |        |
|-------------|--------|
| Length      | 133 mm |
| Width       | 105 mm |
| Dimension a | 105 mm |
| Dimension b | 133 mm |

### Technical data

|                                   |           |
|-----------------------------------|-----------|
| Version for                       | Universal |
| Type                              | coupling  |
| Halogen-free                      | yes       |
| Trunking depth                    | 133 mm    |
| With equipotential bonding        | yes       |
| ROHS-conformant                   | yes       |
| Protection rating                 | IP30      |
| Protection rating IK code         | IK10      |
| Permitted temperature range, max. | 60 °C     |
| Permitted temperature range, min. | -25 °C    |