

# Technical data sheet

## Device support SL 2GT20110

Item number: 6132250



Device support with pre-terminated double protective contact socket for the skirting trunking in the trunking width 110 mm.  
Screwed to the wall above the trunking system.



**PVC** Polyvinylchloride

### Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 6132250                  |
| Type                               | SL2GT20110 rws           |
| Description 1                      | Mounting box             |
| Description 2                      | SL double 20x110 9010    |
| Manufacturer                       | OBO                      |
| Colour                             | Pure white; RAL 9010     |
| Material                           | Polyvinylchloride        |
| Smallest sales unit                | 1                        |
| Unit of quantity                   | Piece                    |
| Weight                             | 15.4 kg                  |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,4822 kg CO2e / 1 Piece |


# Technical data sheet

Device support SL 2GT20110

Item number: 6132250



## Dimensions



|        |        |
|--------|--------|
| Length | 52 mm  |
| Width  | 111 mm |
| Height | 176 mm |

## Technical data

|                                   |                              |
|-----------------------------------|------------------------------|
| Number of units                   | 1                            |
| Equipment                         | 2x protective contact socket |
| Decoration                        | Without                      |
| Halogen-free                      | no                           |
| Accessory mounting type           | Pre-equipped                 |
| Protection rating                 | IP40                         |
| Protection rating IK code         | IK06                         |
| Permitted temperature range, max. | 60 °C                        |
| Permitted temperature range, min. | -5 °C                        |