

Technical data sheet

LCIS 60 cable ladder, 3 m C30 FS

Item number: 6209612



Cable ladder with a 60 mm side height with welded C30 profile rungs which are open in an upwards direction. Rolled side rail for reinforcement and as edge protection. Fastening to the bracket is done using hold-down clamps, type LKS 40. The slot dimension of the rung is 16.5 mm, the appropriate clamp clip 2056 H foot, type BS ..
Magnetic shield insulation without cover 10 dB, with cover 15 dB.



St	Steel
FS	Strip galvanised

Master data

Item number	6209612
Type	LCIS 630 3 FS
Description 1	Cable ladder
Description 2	perforated rung, welded
Manufacturer	OBO
Dimension	60x300x3000
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	3
Unit of quantity	Metre
Weight	288.67 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	7,0024 kg CO2e / 1 Meter


Technical data sheet

LCIS 60 cable ladder, 3 m C30 FS

Item number: 6209612



Dimensions



Length	3,000 mm
Width	300 mm
Height	60 mm
Dimension B	300 mm
Rung slot dimension	17.00

Technical data

Version of the rungs	Profile perforated
Side rail version	Flat profile
Fastening of rung	Welded
Mounting system fastening type	Floor Ceiling Wall
Maintain electrical functions	no
Usable cross-section	120 cm ²
Usable cross-section	12000 mm ²
ROHS-conformant	yes
Rustproof steel, pickled	no
Side perforation	yes
Rung distance	300 mm
Wide-span version	no
Rail thickness	1.5 mm

Technical data sheet


LCIS 60 cable ladder, 3 m C30 FS

Item number: 6209612



Loads

Insertable support spacings, min.	1.5 m
Insertable support spacings, max.	5 m
Support spacing 1.5 m	3.3 kN/m
Support spacing 2.0 m	2 kN/m
Support spacing 2.5 m	1.3 kN/m
Support spacing 3.0 m	1 kN/m
Support spacing 3.5 m	0.78 kN/m
Support spacing 4.0 m	0.4 kN/m
Support spacing 4.5 m	0.3 kN/m
Support spacing 5.0 m	0.2 kN/m



Load diagram, cable ladder, type LCIS 60

- 1 Permitted cable tray/ladder load in kN/m without man load
- 2 Support width in m
- 3 Rail bend in mm at permitted kN/m
- 4 Load scheme during testing
- Load curve with cable tray/ladder width in mm
- Strut bend curve according to support width