


Technical data sheet

Cable ladder LG 110, 6 m VS A2

Item number: 6216499



Cable ladder with perforated side rail of side height 110 mm with riveted C profile rungs, open in an upwards direction. The cable ladder is shipped folded up.

You can find the appropriate U clamp of type 2056 in the vertical ladder systems chapter.

Magnetic shield insulation without cover 10 dB, with cover 15 dB.



A2 Stainless steel

2B Bright, treated

Master data

Item number	6216499
Type	LG 116 VS6 A2
Description 1	Cable ladder
Description 2	perforated, with VS rung
Manufacturer	OBO
Dimension	110x600x6000
Colour	stainless steel
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	6
Unit of quantity	Metre
Weight	468.666 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	24,1896 kg CO2e / 1 Meter


Technical data sheet

Cable ladder LG 110, 6 m VS A2

Item number: 6216499



Dimensions



Dimension	110x600
Length	6,000 mm
Width	600 mm
Height	110 mm
Dimension B	600 mm
Rung slot dimension	16.50

Technical data

Fastening of rung	Blind riveted
Mounting system fastening type	Floor Ceiling Wall
Usable cross-section	568 cm ²
Usable cross-section	56800 mm ²
ROHS-conformant	yes
Rung distance	300 mm
Wide-span version	no
Rail thickness	1.5 mm

Loads

Insertable support spacings, min.	2 m
Insertable support spacings, max.	6 m
Support spacing 2.0 m	3.1 kN/m
Support spacing 2.5 m	2 kN/m
Support spacing 3.0 m	1.3 kN/m
Support spacing 3.5 m	0.9 kN/m
Support spacing 4.0 m	0.6 kN/m
Support spacing 4.5 m	0.5 kN/m
Support spacing 5.0 m	0.45 kN/m
Support spacing 6.0 m	0.15 kN/m