

Technical data sheet

Cable duct, type LKM 20030

Item number: 6248470



Duct cover and base with base perforation. Equipotential bonding is guaranteed between the cover and the base without any additional aids. The LKM cable duct, type LKM 20030, has been tested for the maintenance of electrical function as a routing system according to DIN 4102 Part 12. Please note the cable types tested in the BSS fire protection systems division!



St	Steel
FSK	Strip galvanised / plastic coated

Master data

Item number	6248470
Type	LKM20030RW
Description 1	Cable trunking
Description 2	with base perforation
Manufacturer	OBO
Dimension	20x30x2000
Colour	Pure white; RAL 9010
Material	Steel
Surface	Strip galvanised / plastic coated
Surface standard	DIN EN 10346
Smallest sales unit	2
Unit of quantity	Metre
Weight	61 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	1,3159 kg CO2e / 1 Meter


Technical data sheet

Cable duct, type LKM 20030

Item number: 6248470



Dimensions



Length	2,000 mm
Width	30 mm
Height	24 mm

Technical data

Number of fixed partitions	0
Number of cables NYM 3 x 1.5 mm ² Ø 10.5 mm (without socket)	2
Number of cables NYM 3 x 2.5 mm ² Ø 11.5 mm (without socket)	2
Number of cables NYM 5 x 1.5 mm ² Ø 12.0 mm (without socket)	2
Number of insertable partitions	0
Version, cable trunking cover	Loose
Fastening type	Base perforation
Base perforation	with base perforation
Maintain electrical functions	yes
Halogen-free	yes
Cable retaining clip	no
Duct connector	no
Delivery on a roll	no
Usable cross-section	616 mm ²
ROHS-conformant	yes
Protection rating	IP30
Protective film	no
Protection rating IK code	IK10
Permitted temperature range, max.	90 °C
Permitted temperature range, min.	-5 °C
Transparent	no