

Technical data sheet

US 7 support A2

Item number: 6338704



Suspended support (U profile) with welded head plate.
For fastening to horizontal concrete ceilings and steel girders. For bracket widths of 400 mm or more, or if the bracket is mounted at the end of a suspended support, we recommend the use of the spacer, type DSK 61.



A2 Stainless steel

2B Bright, treated

Master data

Item number	6338704
Type	US 7 K 110 A2
Description 1	Support
Description 2	with welded head plate
Manufacturer	OBO
Dimension	70x50x1100
Colour	stainless steel
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	531 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	33,6778 kg CO2e / 1 Piece


Technical data sheet

US 7 support A2

Item number: 6338704



Dimensions



Length	1,100 mm
Width	70 mm
Height	50 mm

Technical data

Type of perforation	3 sides perforated
Version for	U profile
Bracket length 200	8.3 kN
Bracket length 400	5 kN
Bracket length 600	3.5 kN
Maintain electrical functions	no
Material thickness	4 mm
Maximum tensile load	11 kN
ROHS-conformant	yes


Technical data sheet

US 7 support A2

Item number: 6338704



Loads



Load diagram, U support, type US 7 K VA

- 1 Bending of the end of the suspended support at permitted bracket load
- 2 Permitted bracket load in kN without man load
- 3 Bracket length in mm
- Load curves with support lengths in mm

Characteristic anchor load values for U support, type US 7 K

Single-sided load

Anchor type	Max. load [kN]					
	Bracket width [mm]					
	110%	210	310	410	510	610
BZ3 10x90/0-30	3.97	3.03	2.44	2.04	1.76	1.54
BZ3 12x110/0-35	5.16	3.90	3.15	2.64	2.27	1.99

Max. total load F = cable weight + cable tray + bracket + suspended support. The tabular values for double-sided loads take the available axis spacing $a_i = 10$ cm into account. The stated values are based on uncracked concrete of compressive strength C20/25. Please comply with the installation conditions of ETA(anchors).