

Technical data sheet

US 3 support A4

Item number: 6342391



Suspended support (U profile) of dimensions 50 x 30 mm with welded head plate.

For fastening to horizontal concrete ceilings and steel girders. For bracket widths of 400 mm or more, or if the bracket is mounted at the end of a suspended support, we recommend the use of the spacer, type DSK 25.



A4	Stainless steel
2B	Bright, treated

Master data

Item number	6342391
Type	US 3 K 70 A4
Description 1	Support
Description 2	with welded head plate
Manufacturer	OBO
Dimension	50x30x700
Colour	stainless steel
Material	Stainless steel 1.4571
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	110 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	7,1994 kg CO2e / 1 Piece


Technical data sheet

US 3 support A4

Item number: 6342391



Dimensions



Length	700 mm
Width	50 mm
Height	30 mm

Technical data

Version for	U profile
Bracket length 200	2.1 kN
Bracket length 400	1.1 kN
Maintain electrical functions	no
Material thickness	2 mm
Maximum tensile load	5 kN
ROHS-conformant	yes


Technical data sheet

US 3 support A4

Item number: 6342391



Loads



Load diagram, U support, type US 3 K

- 1 Bending of the end of the suspended support at permitted bracket load
- 2 Permitted bracket load in kN without man load
- 3 Bracket length in mm
- Load curves with support lengths in mm

Characteristic anchor load values for US 3 K suspended support

Anchor type	Single-sided load			
	Max. load [kN]			
	Bracket width [mm]			
	110%	210	310	410
BZ3 8x75/0-20	2.18	1.59	1.25	1.02
BZ3 10x90/0-30	3.05	2.00	1.49	1.18

Max. Max. total load F = cable weight + cable tray + bracket + suspended support.

The values in the table for loading on both sides take into account the existing centre distance $a_i = 10$ cm.

The stated values are based on cracked concrete of the resistance class C20/25. Please comply with the installation requirements of the ETA approval (anchors).