

# Technical data sheet

## Wall and support bracket AW 30

Item number: 6443346



Wall and support bracket with welded head plate of width 410 mm.  
Fastening of the bracket to the U support of width 400 mm or greater using hexagonal bolt through both sides of the support. Please insert suitable spacers.



|    |                 |
|----|-----------------|
| A4 | Stainless steel |
| 2B | Bright, treated |

### Master data

|                     |                               |
|---------------------|-------------------------------|
| Type                | AW 30 41 A4                   |
| Manufacturer        | OBO                           |
| Material            | Stainless steel, grade 316 Ti |
| Surface             | Bright, reworked              |
| Surface standard    |                               |
| Smallest sales unit | 1                             |
| Unit of quantity    | Units                         |
| Weight              | 85.2 kg                       |
| Weight unit         | kg/100 pairs                  |

### Dimensions

|             |        |
|-------------|--------|
| Length      | 410 mm |
| Width       | 410 mm |
| Height      | 80 mm  |
| Dimension A | 50 mm  |
| Dimension B | 410 mm |
| Dimension H | 80 mm  |

### Features/properties/dimensions

|                               |                          |
|-------------------------------|--------------------------|
| Version for                   | Wall and support bracket |
| F in kN                       | 3 kN                     |
| Maintain electrical functions | no                       |
| Hole diameter                 | 13 mm                    |
| Rustproof steel, pickled      | no                       |
| Angle range, max.             | 90 mm                    |
| Angle range, min.             | 90 mm                    |


# Technical data sheet

## Wall and support bracket AW 30

Item number: 6443346



### Loads



#### Load diagram, bracket, type AW 30

- 1 Bending of the bracket tip at permitted bracket load
- 2 Permitted bracket load in kN without man load
- Load curve with bracket lengths in mm