


Technical data sheet

Centre suspension for cable trays with rolled side rail FS

Item number: 6358500



Centre suspension for cable trays
Maximum side height of the cable tray 60 mm. On filling, please ensure an even load distribution (no one-sided filling).



St	Steel
FS	Strip galvanised

Master data

Item number	6358500
Type	MAH 050 FS
Description 1	Centre suspension
Description 2	for cable tray
Manufacturer	OBO
Dimension	B50mm
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,1479 kg CO2e / 1 Piece


Technical data sheet

Centre suspension for cable trays with rolled side rail FS

Item number: 6358500



Dimensions



Length	40 mm
Width	50 mm
Height	39.5 mm
Dimension B	47 mm
Dimension B1	26 mm

Technical data

Version for	Suspended
Maintain electrical functions	no
for width max.	50 mm
for width min.	50
Suitable for metric threaded rod	8
Suitable for mesh cable tray	no
Suitable for cable ladder	no
Suitable for cable tray	yes
Suitable for tray/ladder width	50 mm
Hole diameter	8.5 mm
ROHS-conformant	yes
Adjustable	no