


# Technical data sheet

## Wall bracket AW 80

Item number: 6417884



Heavy-duty wall bracket with welded head plate.  
When fastening cable trays and ladders with truss-head bolts of size M6, please order large washers separately (perforation in bracket 9 x ...).



St

Steel

FT

Hot-dip galvanised

### Master data

|                                    |                           |
|------------------------------------|---------------------------|
| Item number                        | 6417884                   |
| Type                               | AW 80 81 FT               |
| Description 1                      | Wall bracket              |
| Description 2                      | with welded head plate    |
| Manufacturer                       | OBO                       |
| Dimension                          | B810mm                    |
| Colour                             | zinc                      |
| Material                           | Steel                     |
| Surface                            | Hot-dip galvanised        |
| Surface standard                   | DIN EN ISO 1461           |
| Smallest sales unit                | 1                         |
| Unit of quantity                   | Piece                     |
| Weight                             | 623 kg                    |
| Weight unit                        | kg/100 pc.                |
| CO2 Footprint (GWP) Cradle-to-Gate | 15,4548 kg CO2e / 1 Piece |


# Technical data sheet

## Wall bracket AW 80

Item number: 6417884



### Dimensions




|             |        |
|-------------|--------|
| Length      | 60 mm  |
| Width       | 810 mm |
| Height      | 260 mm |
| Dimension A | 60 mm  |
| Dimension B | 810 mm |
| Dimension H | 260 mm |

### Technical data

|                               |                          |
|-------------------------------|--------------------------|
| Version for                   | Wall and support bracket |
| F in kN                       | 8 kN                     |
| Maintain electrical functions | no                       |
| Hole diameter                 | 17.5 mm                  |
| ROHS-conformant               | yes                      |
| Rustproof steel, pickled      | no                       |
| Angle range, max.             | 90 mm                    |
| Angle range, min.             | 90 mm                    |

### Loads



#### Load diagram, bracket, type AW 80

- 1** Bending of the bracket tip at permitted bracket load
- 2** Permitted bracket load in kN without man load
- Load curve with bracket lengths in mm

### Characteristic anchor load values for wall bracket AW 80

| Wall fastening  |                    |      |      |      |      |      |      |
|-----------------|--------------------|------|------|------|------|------|------|
| Anchor type     | Max. load [kN]     |      |      |      |      |      |      |
|                 | Bracket width [mm] |      |      |      |      |      |      |
|                 | 210                | 310  | 410  | 510  | 610  | 710  | 810  |
| BZ3 16x135/0-35 | 7.31               | 7.66 | 6.87 | 6.38 | 5.90 | 5.17 | 4.69 |

Max. total load F = cable weight + cable tray + bracket. The load capacity values increase considerably when used in uncracked concrete. The values given are based on concrete of strength class C20/25. Observe the installation conditions of the DIBt approval (anchors).