


# Technical data sheet

90° vertical bend, rising 110 FT

Item number: 7007400



90° rising vertical bend, for all cable tray types of 110 mm side height.  
The vertical bend is pushed over the end of the cable tray and screwed tight.  
Fastening materials should be ordered separately.



**St** Steel

**FT** Hot-dip galvanised

## Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 7007400                  |
| Type                               | RBV 120 S FT             |
| Description 1                      | 90° vertical bend        |
| Description 2                      | rising                   |
| Manufacturer                       | OBO                      |
| Dimension                          | 110x200                  |
| Colour                             | zinc                     |
| Material                           | Steel                    |
| Surface                            | Hot-dip galvanised       |
| Surface standard                   | DIN EN ISO 1461          |
| Smallest sales unit                | 1                        |
| Unit of quantity                   | Piece                    |
| Weight                             | 163 kg                   |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 5,0724 kg CO2e / 1 Piece |


# Technical data sheet

90° vertical bend, rising 110 FT

Item number: 7007400



## Dimensions



|                 |        |
|-----------------|--------|
| Width           | 200 mm |
| Width           | 8 in   |
| Height          | 110 mm |
| Height          | 4 in   |
| Plate thickness | 1 mm   |
| Dimension B     | 200 mm |

## Technical data

|                                         |                    |
|-----------------------------------------|--------------------|
| Bend (angle)                            | 90°                |
| Connector version                       | Without connectors |
| Maintain electrical functions           | no                 |
| Mounting perforation in base            | no                 |
| NATO hole pattern                       | no                 |
| Change of direction                     | Vertical rising    |
| ROHS-conformant                         | yes                |
| Rustproof steel, pickled                | no                 |
| Side perforation                        | no                 |
| Wide-span version                       | no                 |
| Type of connector, cable support system | Screwed            |