

Technical data sheet

EI60 90° bend for PLCS D061220 fire protection duct

Item number: 7217884



90° bend for PYROLINE® Con S EI60 fire protection duct, type PLCS D061220, consisting of fibre glass light concrete which is resistant to water and frost for the creation of horizontal changes of direction of the duct. Mounted connectors ensure quick mounting in situ, whilst loosely placed covers ensure quick inspection and reassignment.

Including connection screws and sealing strips.
Including connection screws and sealing strips.



Fibreglass lightweight concrete

Master data

Item number	7217884
Type	PLCS B061220
Description 1	90° bend EI60
Description 2	for PLCS D061220
Manufacturer	OBO
Dimension	200x120
Colour	Grey
Material	Fibreglass lightweight concrete
Smallest sales unit	1
Unit of quantity	Piece
Weight	1180 kg
Weight unit	kg/100 pc.


Technical data sheet

EI60 90° bend for PLCS D061220 fire protection duct

Item number: 7217884



Dimensions



External dimensions	308 x 190
Internal dimensions	120 x 200
Dimension B	308 mm
Dimension b	200 mm
Dimension h	120 mm
Dimension H	190 mm
Dimension L	410 mm

Technical data

Number of flammable sides	4
Cover fastening	Loose
Classification EI – installation duct	60
With perforation	no
ROHS-conformant	yes
Jacketing	Without
Material of the insulation	Glass-fibre lightweight concrete
Angle of the bend	90 °