

Technical data sheet

Wall and support bracket MWAM 12

Item number: 6424550



Light-duty wall and support bracket including quick connector for use with cable trays of type RKSM.

Wall and support bracket MWAM.. including:

1. Two pre-mounted quick connectors for efficient cable tray fastening.
2. Truss-head bolt M10 x 25 for fastening on the U support.
Including truss-head screw M10 x 25 for fastening to U supports.



St	Steel
FS	Strip galvanised

Master data

Item number	6424550
Type	MWAM 12 11 FS
Description 1	Wall and support bracket
Description 2	including quick fastening
Manufacturer	OBO
Dimension	B110mm
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	19.5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0.5312 kg CO2e / 1 Piece

Dimensions

Length	32.5 mm
Width	110 mm
Width	4 in
Height	53 mm
Height	2.09 in
Dimension A	32.5 mm
Dimension B	110 mm
Dimension H	53 mm
Dimension W	110 mm

Technical data sheet

Wall and support bracket MWAM 12


Item number: 6424550



Technical data

Version for	Wall and support bracket
F in kN	1.2 kN
Maintain electrical functions	no
Hole diameter	11 mm
ROHS-conformant	yes
Rustproof steel, pickled	no
Angle range, max.	90 mm
Angle range, min.	90 mm

Loads



Load diagram, bracket type MWAM 12

- 1** Bending of the bracket tip at permitted bracket load
- 2** Permitted bracket load in kN without man load
- Load curve with bracket lengths in mm

Characteristic anchor load values for wall and support bracket MWAM 12

Wall fastening	Max. load [kN]			
	Bracket width [mm]			
Anchor type	110	210	310	410
BZ3 10x90/0-30	1.2	1.2	1.2	1.2

Max. Belastung F ges. = Kabelgewicht + Kabelrinne + Ausleger. Die angegebenen Werte basieren auf gerissenem Beton der Festigkeitsklasse C20/25. Die Einbaubedingungen der ETA-Zulassung (Dübel) sind zu beachten!

Load values for MWAM 12 on support

Support	Max. total load F in kN			
	Bracket length in mm			
	100	200	300	400
US 3 K/ 20 - 60	1.2	1.2	1.2	1.2
US 3 K/ 70 - 120	1.2	1.2	1.2	1.2
US 5 K/ 20 - 60	1.2	1.2	1.2	1.2
US 5 K/ 70 - 120	1.2	1.2	1.2	1.2

