

Technical data sheet

Profile rail, heavy duty, slot width 18 mm, perforated, FT

Item number: 1121873



Heavy-duty C profile rail for the individual installation of support constructions, e. g. for cable trays or as a panel for switchgear cabinets. Can also be used for cable routing, in conjunction with clamp clips with a U foot.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	1121873
Type	MS4022P1100FT
Description 1	Profile rail
Description 2	perforated, slot 18mm
Manufacturer	OBO
Dimension	1100x40x22,5
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	167.75 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	3,6654 kg CO2e / 1 Piece


Technical data sheet

Profile rail, heavy duty, slot width 18 mm, perforated, FT

Item number: 1121873



Dimensions



Length	1,100 mm
Width	40 mm
Height	22.5 mm
Dimension L	1,100 mm

Technical data

Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	50 mm
Maintain electrical functions	yes
Hole width	13 mm
Hole shape (ETIM)	Long slot
Hole size	30x13
Material thickness	2 mm
With perforation	yes
Profile shape	C profile
Slot width	18 mm
Static value A	1.74 cm ²
Static value I _y	1.86 cm ⁴
Static value I _z	4.46 cm ⁴
Static value W _y	1.05 cm ³
Static value W _z	2.23 cm ³