

Technical data sheet

Vertical ladder, SLM50

Item number: 6010004



Heavyweight vertical ladder system for the maintenance of electrical function to DIN 4102 Part 12. Approved clips, type BS-U1-M-... FT. Supplied unmounted. Rungs, type C 40/..., and bolts, type FRS 8 x 35, are supplied unmounted with rail profiles. Rung distance: 300 mm

St	Steel
FT	Hot-dip galvanised

Master data

Item number	6010004
Type	SLM50C40F 20 FT
Description 1	Vertical ladder
Description 2	rung distance 300 mm
Manufacturer	OBO
Dimension	200x3000mm
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	3
Unit of quantity	Metre
Weight	628.333 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	13,7865 kg CO2e / 1 Meter


Technical data sheet

Vertical ladder, SLM50

Item number: 6010004



Dimensions



Length	3,000 mm
Width	200 mm
Height	50 mm
Dimension B	200 mm
Rung slot dimension	2.00

Technical data

Side wall version	Profile (open)
Version of the rungs	Profile unperforated
Maintain electrical functions	yes
ROHS-conformant	yes
Rustproof steel, pickled	no
Side perforation	yes
Rung distance	300 mm