


Technical data sheet

Cross-over 85 FS

Item number: 7027333



Cross-over for the creation of a horizontal branch, fitting for lock and screw-on cable trays of side height 85 mm. Screwless mounting with double clamps or screw connection with FRS truss-head screws and M6 combination nuts. Can be used in indoor areas. Fastening material must be ordered separately.



St	Steel
FS	Strip galvanised

Master data

Item number	7027333
Type	RK 820 FS
Description 1	Cross over
Description 2	for cable tray
Manufacturer	OBO
Dimension	85x200
Colour	zinc
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	1
Unit of quantity	Piece
Weight	150.4 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	5,3641 kg CO2e / 1 Piece


Technical data sheet

Cross-over 85 FS

Item number: 7027333



Dimensions



Width	200 mm
Height	85 mm
Plate thickness	0.8 mm
Dimension B	200 mm
Dimension R	50 mm

Technical data

Connector version	Integrated connector
Maintain electrical functions	no
Material thickness, floor plate	0.8 mm
NATO hole pattern	no
ROHS-conformant	yes
Rustproof steel, pickled	no
Permitted temperature range, max.	120 °C
Permitted temperature range, min.	-20 °C
Wide-span version	no
Type of connector, cable support system	screwed/clamped
Recommended quantity of bolts	32 St.
Rail thickness	1.25 mm