

Technical data sheet

Cable ladder LG 60, 6 m VS FT SOMY

Item number: 7188633



Cable ladder with 60 mm side height with riveted C profile rungs which are open in an upwards direction.

The cable ladder is shipped folded up. The surface coating is a coating created in a single-dip method with extra-high zinc thicknesses.

Magnetic shield insulation without cover 10 dB, with cover 15 dB.



St	Steel
FT SO	Hot-dip galvanised 85 µm

Master data

Item number	7188633
Type	LG 640 VS 6 FTSO
Description 1	Cable ladder
Description 2	perforated, with VS rung
Manufacturer	OBO
Dimension	60x400x6000
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised 85 µm
Surface standard	DIN EN ISO 1461
Smallest sales unit	6
Unit of quantity	Metre
Weight	342.2 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	7,4612 kg CO2e / 1 Meter


Technical data sheet

Cable ladder LG 60, 6 m VS FT SOMY

Item number: 7188633



Dimensions



Dimension	60 x 400
Length	6,000 mm
Width	400 mm
Height	60 mm
Dimension B	400 mm
Rung slot dimension	16.50

Technical data

Version of the rungs	Profile perforated
Side rail version	Flat profile
Fastening of rung	Blind riveted
Mounting system fastening type	Floor Ceiling Wall
Maintain electrical functions	no
Usable cross-section	198 cm²
Usable cross-section	19800 mm²
ROHS-conformant	yes
Rustproof steel, pickled	no
Side perforation	yes
Rung distance	300 mm
Wide-span version	no
Rail thickness	1.5 mm

Technical data sheet


Cable ladder LG 60, 6 m VS FT SOMY

Item number: 7188633



Loads

Insertable support spacings, min.	1.5 m
Insertable support spacings, max.	5 m
Support spacing 1.5 m	3.1 kN/m
Support spacing 2.0 m	2.25 kN/m
Support spacing 2.5 m	1.5 kN/m
Support spacing 3.0 m	1.1 kN/m
Support spacing 3.5 m	0.75 kN/m
Support spacing 4.0 m	0.45 kN/m
Support spacing 4.5 m	0.3 kN/m
Support spacing 5.0 m	0.15 kN/m



Load diagram, cable ladder, type LG 60 VS

- 1 Permitted cable tray/ladder load in kN/m without man load
- 2 Support width in m
- 3 Rail bend in mm at permitted kN/m
- 4 Load scheme during testing
- Load curve with cable tray/ladder width in mm
- Strut bend curve according to support width