

Technical data sheet

IS 8 support FT SOMY

Item number: 7193319



I support in fixed lengths. Dimensions 80 x 42 mm.
Single and double-sided brackets of type AS 15, AS 30 and AS 55 can be fastened to the IS 8 I support. The height of the brackets is infinitely adjustable.
The surface coating is a coating created in a single-dip method with extra-high zinc thicknesses.



St	Steel
FT SO	Hot-dip galvanised 85 µm

Master data

Item number	7193319
Type	IS 8 600 FT SO
Description 1	I support
Manufacturer	OBO
Dimension	80x42x6000
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised 85 µm
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	3460 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	10,3358 kg CO2e / 1 Piece


Technical data sheet

IS 8 support FT SOMY

Item number: 7193319



Dimensions



Dimension	80 x 42
Length	6,000 mm
Width	80 mm
Height	42 mm

Technical data sheet

IS 8 support FT SOMY

Item number: 7193319



Technical data

Breakable	no
Type of perforation	Perforated bar
Version for	Single profile
Maintain electrical functions	no
Hole width	14 mm
With toothing	no
Profile shape	I profile
ROHS-conformant	yes
Slot width	70 mm
Static value A	7.02 cm ²
Static value I _y	6.26 cm ⁴
Static value I _z	77.53 cm ⁴
Static value W _y	2.98 cm ³
Static value W _z	19.38 cm ³

Characteristic anchor load values for IS 8 support

Fastening on the wall / entire length	Max. total load F in kN					
	Bracket length in mm					
Anchor type	100	200	300	400	500	600
BZ-U 10-10/90	7.80	6.78	5.95	5.17	4.64	4.14
BZ 70 M12-15/110	11.35	8.25	7.63	7.11	6.47	5.38

Max. Max. total load F = cable weight + cable tray + bracket + support. The load capacity values increase considerably when used in uncracked concrete. Observe the load capacity of the brackets (diagram) and the installation conditions of the DIBt approval (anchors).