

Technical data sheet

Ceramic terminal, double

Item number: 7205705



High-temperature-resistant ceramic terminal with four connection options for refitting of the FireBox T series. Tested according to DIN EN 60998-2-1:2004.



Steatite

Master data		
Item number	7205705	
Type	TK 10-2	
Description 1	Ceramic terminal	
Description 2	for FireBox T	
Manufacturer	OBO	
Dimension	10 mm²	
Colour	Cream	
Material	Steatite	
Smallest sales unit	5	
Unit of quantity	Piece	
Weight	4.2 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,0079 kg CO2e / 1 Piece	


Technical data sheet

Ceramic terminal, double

Item number: 7205705



Dimensions



Length	24.5 mm
Width	26.5 mm
Height	26 mm

Technical data

Closing plate required	no
Connectable conductor cross-section, single-wire, max.	10 mm ²
Connectable conductor cross-section, single-wire, min.	4 mm ²
Connection position	Side
No. of terminals	4
Number of screwless terminals per pole	4
Version of electrical connection 1	Screw connection
Version of electrical connection 2	Screw connection
Explosion-tested version	no
Insulation material	Ceramic
Mounting type	Miscellaneous
Nominal cross-section, max.	10 mm ²
Nominal cross-section, min.	4 mm ²
Nominal voltage	400 V
Nominal current	57 A
Pole number	1
Permitted temperature range, max.	250 °C
Permitted temperature range, min.	0 °C
Transparent	no