


Technical data sheet

Rising vertical bend for PYROLINE® Con S BSKH09-K0511 fire protection duct Item number: 7215652



Rising vertical bend for PYROLINE® Con S fire protection duct, BSKH09-K0511, consisting of fibreglass lightweight concrete which is resistant to water and frost for the creation of vertical changes of direction (45°) of the duct. Mounted connectors ensure quick mounting in situ, whilst loosely placed covers ensure quick inspection and reassignment.

Including connection screws and sealing strips.
Including connection screws and sealing strips.



Fibreglass lightweight concrete

Master data


Item number	7215652
Type	BSKH09-VS0511
Description 1	Vertical bend rising
Description 2	for BSKH09-K0511
Manufacturer	OBO
Dimension	50x110
Colour	Grey
Material	Fibreglass lightweight concrete
Smallest sales unit	1
Unit of quantity	Piece
Weight	648 kg
Weight unit	kg/100 pc.

Technical data sheet

Rising vertical bend for PYROLINE® Con S BSKH09-K0511
fire protection duct
Item number: 7215652



Dimensions



External dimensions	238 x 140
Internal dimensions	110 x 50
Width	238 mm
Dimension B	238 mm
Dimension b	110 mm
Dimension h	50 mm
Dimension H	140 mm
Dimension L	204 mm

Technical data

Number of flammable sides	4
Cover fastening	Loose
Fire resistance class E – function maintenance	30
Fire resistance class I – installation duct	90
With perforation	no
ROHS-conformant	yes
Partitions possible	yes
Jacketing	Without
Material of the insulation	Glass-fibre lightweight concrete
Angle of the bend	45 °