


Technical data sheet

Height-adjustable, decouplable cassette for tube body, stainless steel

Item number: 7409497



Height-adjustable and decouplable round cassettes are suitable for flush floor device installation in UGD-3 underfloor connection boxes. Depending on the design, they are suitable for dry, moist or wet-cleaned floors. The cassette rests on the fixing bracket fastened in the top frame of the box, using which the cassette can be adjusted to the top edge of the floor covering. The fixing bracket decouples the cassette from the raw ceiling. The connection socket must have an appropriate installation opening and, for this reason, needs a blanking lid with an appropriate installation opening. The cassettes are made from stainless steel or brass. All the cassettes contain a 4 mm thick sheet steel plate, for safe absorption of the traffic loads. The cassettes are available for different floor covering thicknesses of 20 and 25 mm.

Height-adjustable cassette with tube body. For the installation of 3 universal supports UT4 for 9 single installation devices with support ring/support clamp or

12 Modul **45®** devices. The delivery includes a screed protection lid made from aluminium (can be sanded), a matching mounting lid for fixing the cassette tube body and an ISO apron for the decoupling of the underfloor connection socket.



A2 Stainless steel

Master data

Item number	7409497
Type	TRKRFN 9 VS 250
Description 1	Cassette for seamless floors
Description 2	round, tube body
Manufacturer	OBO
Dimension	Ø304x85
Material	Stainless steel 1.4301
Smallest sales unit	1
Unit of quantity	Piece
Weight	840.6 kg
Weight unit	kg/100 pc.


Technical data sheet

Height-adjustable, decouplable cassette for tube body,
stainless steel

Item number: 7409497



Dimensions



Technical data

Number of installable devices	12
Number of cable outlets	1
Number of universal supports	3 x UT4
Cover version	Round
Cable outlet version	Lowerable tube body
Floor care	Wet
Decouplable	yes
Floor height, min.	140 mm
Suitable for raised floor installation	no
Suitable for cavity floor installation	no
Suitable for	Underfloor socket structure
Suitable for underfloor box	250
Device support to accept mounting boxes	no
Nominal size for device installation units	R9
Height-adjustment range, max.	113 mm
Height-adjustment range, min.	73 mm
Standard	EN 50085-2-2
ROHS-conformant	yes
Protection rating (IP) when used	IP20
Protection rating (IP) when unused	IP44
Protection rating IK code	IK10
Heavy-duty version	no
Installation system type	UT4
Vertical load, large area	to 5,000 N
Vertical load, small area	to 3,000 N
Approvals	VDE
Floor covering thickness	25 mm