


Halogen-free cable routing and device installation systems

Low smoke gas production, low corrosion, safe.



A safe choice in public areas

OBO halogen-free cable routing systems protect people, the environment and property. All the products are made from high-quality PC/ABS (polycarbonate/acrylonitrile butadiene styrene). This material is one of the self-extinguishing plastics.



Heavy smoke development

Flame-protection agents, based on halogen compounds such as fluorine, iodine, chlorine and bromine, are used to keep the flammability of PVC low. This aspect, which actually increases safety, can turn into a dangerous disadvantage during a fire, as toxic smoke gases, such as carbon dioxide and carbon monoxide, are created.



These usually endanger people far more quickly than flames and heat. For example, in the catastrophic fire at Düsseldorf Airport in 1996 or in the Tauern Tunnel in 1999, considerable quantities of burned plastics contributed to the formation of smoke and hazardous substances. A highly toxic mixture, which can be lethal after just a few breaths.

Protecting existing buildings better

To guarantee increased property protection in the event of a fire, and to prevent the damage and costs following a fire, halogen-free cable routing systems (made of PC/ABS) must be installed in many public buildings. Standard PVC releases corrosive hydrogen chlorine gas, which, in conjunction with the moisture of the extinguishing water, forms hydrochloric acid. Hydrochloric acid presents various risks: On the one hand, it is damaging to health, as it has an irritant effect on the respiratory tracts, and, on the other hand, it attacks the substance of buildings as it eats away at metals and, as an electrically conductive substance, can lead to short circuits. This is why all the halogenfree cable routing systems meet the requirements of DIN EN 50085.

Rapid 45-2 GKH device installation trunking, halogen-free plastic

Device installation trunking system with 45 mm system opening for direct installation of switching and plug-in devices from the Modul 45 series





			76		F + 7	10
	Internal corner	T piece	End piece	Partition	Joint cover	Joint cover
GKH-53100 Trunking height 53 mm Trunking width 100 mm	6113065	6113100	6113110	6114166	6113020	6113030

Colour: Pure white You can find our comprehensive overall system in the "Device installation trunking and poles" catalogue.



Overview, Rapid 80 GKH device installation trunking, halogen-free plastic

Device installation trunking with 80 mm system opening for installation of switching and connecting devices in device installation sockets

HALOGEN FREE								
		Device	Trunking	External	External	External	Flat	Flat
		installation trunking*	Trunking cover, smooth	corner cover, variable	corner	corner cover, smooth	angle cover	angle
GKH70130 Trunking height 70 mm, Trunking width 130 mm	130	6114200	6114210	6274410	6114220	6114230	6274420	6114240
GKH70170 Frunking height 70 mm, Frunking width 170 mm	170	6114300	6114210	6274610	6114320	6114230	6274620	6114340

Colours: Pure white

You can find our comprehensive overall system in the "Device installation trunking and poles" catalogue.




^{*} One coupling pair is pre-mounted on one side for each trunking length. |


7	11					Jan 1			
Flat angle cover, smooth	Internal corner cover, variable	Internal corner	T piece	End piece	Separating retainer	Duct clamp	Coupling	Accessory mounting box single	Accessory mounting box double
6114250	6274440	6114260	6114270	6114280	6114290	6288640	6274650	6288610	6288608
6114250	6274640	6114360	6114370	6114380	6114290	6288640	6274650	6288610	6288608



Overview WDKH wall and ceiling trunking









Overview WDKH wall and ceiling trunking



				P			
	Wall and ceiling trunking	Internal corner	External corner	Flat angle	T piece	Partition	End piece
WDKH 40060 System size*	6175410	6175594	6175630	6175666	6175702		6175558
40 x 60 mm	6175466	6175972	6176008	6176044	6176080	6175500	6175936
WDKH 60090	6175415	6175598	6175634	6175670	6175706		6175562
System size 60 x 90 mm	6175469	6175976	6176012	6176048	6176084	6175504	6175940
WDKH 60110	6175420	6175602	6175638	6175674	6175710		6175566
System size 60 x 110 mm	6175472	6175980	6176016	6176052	6176088	6175504	6175944
WDKH 60150	6175425	6175606	6175642	6175678	6175714		6175570
System size 60 x 150 mm	6175475	6175984	6176020	6176056	6176092	6175504	6175948

 * The system size may deviate from the dimensions in detail. You can find the exact dimensions in the catalogue or on the Internet. You can find our comprehensive overall system in the "Cable routing systems" catalogue.



Overview, LKVH wiring trunking, halogen-free

DIN wiring trunking system for cable routing in switchgear cabinets



LKVH 50037	LKVH 50050	LKVH 50075	LKVH 75037
Trunking height 50 mm Trunking width 37 mm	Trunking height 50 mm Trunking width 50 mm	Trunking height 50 mm Trunking width 75 mm	Trunking height 75 mm Trunking width 37 mm
6178582	6178585	6178588	6178552

	3	3	4
LKV H H	KNW1	KNW2	KSN1
Wire retainer	Riveting tool for KSN 1	Riveting tool for KSN 22	Spreading rivet 4.5 mm
6178650	6178527	6178529	6178520

Colour: Light grey You can find our comprehensive overall system in the "Cable routing systems" catalogue







LKVH 75050	LKVH 75075	LKVH 75100	LKVH 75125
Trunking height 75 mm Trunking width 50 mm	Trunking height 75 mm Trunking width 75 mm	Trunking height 75 mm Trunking width 100 mm	Trunking height 75 mm Trunking width 125 mm
6178556	6178559	6178563	6178566
+			
KSN22	AKZ	2064 GTPL 2M	2069 2M GTPL
Spreading rivet 6.5 mm	Release pliers	Support rail, perforated	Hat profile rail, perforated
6178525	6178535	1115065	1115669



Overview, LK4H wiring trunking, halogen-free

Wiring trunking system with metric dimensions for cable routing in switchgear cabinets



A CHICADOLDI	A STATE OF THE PARTY OF THE PAR	Le chililididil	THE PROPERTY OF THE PARTY OF TH
LK4H 30030	LK4H 40025	LK4H 40040	LK4H 40060
Trunking height 30 mm Trunking width 30 mm	Trunking height 40 mm Trunking height 25 mm	Trunking height 40 mm Trunking height 40 mm	Trunking height 40 mm Trunking height 60 mm
6132540	6132544	6132546	6132548


LK4H N 80025	LK4H N 80040	LK4H N 80060	LK4H N 80080
Trunking height 80 mm, Trunking height 25 mm	Trunking height 80 mm Trunking height 40 mm	Trunking height 80 mm Trunking height 60 mm	Trunking height 80 mm Trunking height 80 mm
6132560	6132562	6132564	6132566


Colour: Light grey You can find our comprehensive overall system in the "Cable routing systems" catalogue.











OBO Bettermann Holding GmbH & Co. KG

P.O. Box 1120 58694 Menden GERMANY

Customer Service

Tel.: +49 2373 89-17 00 Fax: +49 2373 89-12 38

export@obo.de

www.obo-bettermann.com

OBO Bettermann Order number 9138952 09/2022 INT



